

Which Diaphragm can be used in which Vacuum Shut Off Valve

4161 <i>Greenoak Vacuum Shut Off Valve</i> 	4162 <i>Greenoak Vacuum Shut Off Valve with Resistive Sensor</i> 	4165 <i>Greenoak Vented Vacuum Shut Off Valve</i> 	4167 <i>Greenoak Vacuum Operated Transfer Valve</i> 
---	---	--	--



					Notes
29171 <i>Diaphragm for Greenoak Shut Off Valve 4.3mm x 60mm</i> 	✓			✓	Suits Greenoak valves best.
29171G <i>Diaphragm for Greenoak Shut Off Valve 5mm x 60mm</i> 	✓	✓		✓	Thicker diaphragm - suits Gascioigne valves best. Can also be used in 4161, 4162 and 4167 valves.
29171V <i>Diaphragm for Greenoak Shut Off Valve Vaccar Type 4.3mm x 60mm</i> 	✓	✓		✓	Ideally suits 4162 "Sensor" valve. Can also be used in 4161 and 4167 valves
29172 <i>Service Kit for Vented Shut Off Valve</i> 			✓		For vented valve only
29175 <i>Service Kit for Vented Shut Off Valve</i> 			✓		For vented valve only